



designed for scientists



T 25 digital ULTRA-TURRAX®

/// Data Sheet

High-performance dispersing instrument for volumes from 1 – 2000 ml (H₂O) with digital speed display. It offers a wide speed range from 3000 – 25,000 rpm that enables users to work at high circumferential speeds even with small rotor diameters. A broad choice of dispersing elements adds versatility. Applications ranges from homogenizing waste water samples, use in laboratory reactors, dispersion tasks under vacuum / pressure and sample preparation in medical research.

- Digital speed display
- Electronic speed control

www.ika.com

Subject to technical changes



IKAworlwide



IKAworlwide /// #lookattheblue



@IKAworlwide



designed for scientists

- Electronic overload protection
- Stainless steel dispersing elements can be cleaned quickly and easily
- Plastic disposable dispersing elements are available in two sizes
- Error code display
- Quiet operation

The dispersing tool is not included in the scope of delivery.





designed for scientists

Technical Data

Motor rating input [W]	800
Motor rating output [W]	500
Volume range (H ₂ O) [l]	0.001 - 2
Viscosity max. [mPas]	5000
Speed range [rpm]	3000 - 25000
Speed deviation [%]	1
Speed display	LED
Speed adjustment	stepless
Noise without element [dB(A)]	75
Extension arm diameter [mm]	13
Extension arm length [mm]	160
Process type	batch
Permissible ON time [%]	100
Dimensions (W x H x D) [mm]	87 x 271 x 106
Weight [kg]	2.5
Permissible ambient temperature [°C]	5 - 40
Permissible ambient conditions	80% (up to 31°C), decreasing linearly to max. 50 (@40°C)
Protection class according to DIN EN 60529	IP 20
Voltage [V]	220 - 240
Frequency [Hz]	50/60
Power input [W]	800