


Series 35-45

HOW TO ORDER



BODY TYPE	PORT SIZE	VALVE FUNCTION/MANIFOLD TYPE
<b>Inline</b>	<b>O</b> Manifold Body Only	<b>O</b> Manifold Body Only
<b>A</b> Individual Inline	<b>A</b> 1/8" NPT	<b>B</b> 3 way N.C. Only (Inline)
<b>D</b> Indiv. Inline w/2 Manifold Mount Ports	<b>B</b> #10-32 UNF (Inline Only)	
	<b>C</b> 1/8" BSPPL	
	<b>D</b> M5 (Inline Only)	
	<b>E</b> 1/8" BSPTR	
<b>Manifold</b>		
<b>E</b> Manifold Body (N.C. Only Poppet)		
<b>G</b> Manifold Body w/Gage Port (N.C. Only Poppet)		


Note : there is no manifold base for the 35 series.  
The manifold valve can only mount to a circuit bar, see note below



BODY TYPE	PORT SIZE	VALVE FUNCTION/MANIFOLD TYPE
<b>Inline</b>	<b>O</b> Manifold Body Only	<b>Inline</b>
<b>A</b> 4 Port Body	<b>A</b> 1/8" NPT	<b>1</b> No Flow Controls
<b>B</b> 5 Port Body	<b>B</b> #10-32 UNF	<b>Bases - Regulators</b>
<b>D</b> 4 Port Body "O" Ring Mount -All Bottom Ports	<b>C</b> 1/8" BSPPL	<b>O</b> Valve Only - No Base
<b>E</b> 5 Port Body "O" Ring Mount -3 Bottom Ports Inlet and Cylinders	<b>D</b> M5 (Metric)	<b>A</b> Individual Base
<b>F</b> 4 Port Body "O" Ring Mount-Bottom Cylinder Ports Only	<b>F</b> #10-32 UNF Bottom Ports	<b>C</b> Manifold Base
	<b>G</b> M5 Bottom Ports	<b>E</b> Manifold w/Regulator w/Slotted Stem
	<b>H</b> "O" Ring Mount Ports	<b>G</b> Manifold w/Regulator w/Locking Slotted Stem
	<b>J</b> 1/8" NPT Bottom Ports	<b>J</b> Manifold w/Regulator w/Locking Knob
	<b>K</b> 1/8" BSPPL Bottom Ports	
<b>Base Mount</b>		
<b>O</b> For Base Only - No Valve		
<b>L</b> Base Mount Body		
<b>M</b> Base Mount Body with Gage Port		

MANIFOLD MOUNT ACCESSORIES

- M-45008-01** End Plate Kit
- 16455** Pressure Seal Between Manifold
- 19753** Tie Rod
- N-45008** Isolator Kit - Inlet and Exhaust
- N-45009** Isolator Kit - Inlet only
- N-45010** Isolator Kit - Exhaust only
- N-45015** End Cover Plate - Plain
- N-45016** End Cover Plate w/Flow Controls
- N-45017** Flow Control Needle Assembly



VOLTAGE	LEAD LENGTH	MANUAL OPERATOR	ELECTRICAL CONNECTION
<b>FR</b> 12VDC (0.6 W)	<b>A</b> 18" Leads	<b>0</b> No operator	<b>BA</b> Grommet
<b>FS</b> 24VDC (0.6 W)	<b>B</b> 24" Leads	<b>1</b> Non-locking Recessed	<b>CA</b> Conduit 1/2" NPS†
<b>FV</b> 12VDC (0.4 W)	<b>C</b> 36" Leads	<b>2</b> Locking Recessed	<b>CM</b> Metal Conduit 1/2" NPS†
	<b>D</b> 48" Leads	<b>3</b> Non-locking Extended	<b>CN</b> Metal Conduit w/grd. 1/2" NPS†
	<b>E</b> 72" Leads	<b>4</b> Locking Extended	<b>External Plug-in</b>
	<b>J*</b> 6" Leads		<b>FM</b> Plug-in (For ECD & ECE Bar)
			<b>JB</b> Rectangular Plug-in†
			<b>JM</b> Rectangular Male only†
			<b>KA</b> Mini Plug-in
			<b>KJ</b> Mini Plug-in Male only
			<b>TA</b> Dual Tabs (.110) Plain
			<b>TJ</b> Dual Tabs (.110) Plain

\*Use "J" for external plug-in connectors

NOTE : For valves mounted to a circuit bar reference MAC circuit bar Catalog for ordering info.  
For the 35 series circuit bar, use MOD FM01 after circuit bar part number.

† Available on individual valves and circuit bars.