

ORBi-SHAKER™ XL

MAXIMUM CAPACITY, BENCHTOP MODEL



- + High Capacity, benchtop model
- + Circular 19mm orbit for aeration and mixing
- + Exchange flask clamps in one second with MAGIC CLAMP™ platform.

with **MAGIC CLAMP™**
Patent Pending

Technical Data

Speed Range:	30 to 300 rpm
Speed Increment:	1 rpm
Orbit:	19mm (3/4")
Max. Capacity:	5 x 2L or 9 x 1L Flasks
Max. Load:	65 lbs (30kg)
Platform Dimensions:	17.8 x 17.8 in. / 45 x 45 cm (Included)
Timer:	1 min. to 48 hours / continuous
Weight:	65 lbs / 30 kg
Dimensions:	18.5 x 21.25 x 5 in. / 47 x 54 x 12.5 cm
Electrical:	120V or 230V, 50-60Hz

The Orbi-Shaker XL offers flask capacity that far exceeds most benchtop models. With a large 18 x 18 inch platform and a powerful, beltless motor drive, the Orbi-Shaker XL is capable of mixing up to five 2L flasks or nine 1L flasks simultaneously. The included, non-slip rubber mat platform is ideal for low speed applications, while the convenient MAGIC CLAMP™ platform is also available for high speed mixing of Erlenmeyer flasks, tube racks or microplates. The MAGIC CLAMP™ allows for instant flask clamp exchange without the use of tools, screws or any other hardware.


Ordering Information

BT1010* Orbi-Shaker XL, High capacity, benchtop shaker
Includes 18x18" platform with non-slip mat, 115V

Optional Platforms and Accessories:

H1010-MR	MAGic Clamp universal platform, (18x18")
H1000-MR-50	Flask Clamp, 50ml (max. 49)
H1000-MR-125	Flask Clamp, 125ml (max. 36)
H1000-MR-250	Flask Clamp, 250ml (max. 25)
H1000-MR-500	Flask Clamp, 500ml (max. 16)
H1000-MR-1000	Flask Clamp, 1000ml (max. 9)
H1000-MR-2000	Flask Clamp, 2000ml (max. 5)
H1000-MR-1550	Tube Rack, 20x50 & 30x15 ml tubes (max. 4)
H1000-MR-T15	Tube Rack, 32x15 tubes (max. 8)
H1000-MR-T50	Tube Rack, 15x50 tubes (max. 8)
H1000-MR-T600	Bottle Rack, 4x500/600ml conical bottles (max. 4)
H1000-MR-T15H	Tube Rack, 12 x 1.5/2.0ml horizontal (max. 6)
H1000-MR-T150H	Tube Rack, 4 x 15ml horizontal (max.8)
H1000-MR-T500H	Tube Rack, 2 x 50ml horizontal (max.8)
H1010-P-SP	Spring loaded platform, for uncommon vessels
H1010-P-MP	6 x microplate platform (standard or deepwell)

*To order item in 230V, add (-E) to item number.



Benchmark Scientific

PO Box 709 Edison, NJ 08818
Phone: 908-769-5555 Fax: 732-313-7007
Web: www.BenchmarkScientific.com
Email: Info@BenchmarkScientific.com