


# ORBi-SHAKER™ CO<sub>2</sub>

## Remote Controlled, All Environment Shakers

The new Orbi-Shaker CO<sub>2</sub> series is designed for shaking, mixing & aeration applications in extreme environments, including CO<sub>2</sub> incubators. It can withstand temperatures from 0 to 65°C and humidity levels up to 100%.

To avoid contamination, unintentional release of gas or deviations from protocol, all settings are adjusted via the included remote control module. This module can be stored outside of the chamber and connects to the shaker via a flat (1mm thickness) cable, that easily passes through a port or underneath an incubator door without compromising the seal. This allows for user adjustment of run time or mixing speed without opening the chamber door(s).


The instrument is supplied with a non-slip rubber mat platform. In addition, convenient MAGic Clamp™ platforms (of multiple sizes) are also available for use with Erlenmeyer flasks and test tube racks. The unique magnetic attachment method has been widely recognized as the easiest way to instantly change between flask clamps of different sizes.



Item: BT4001

Compatibility Chart:	SureTherm™ CO <sub>2</sub>		New Brunswick™		Shel Lab®	Thermo® HeraCell™		Fisher®	VWR® Symphony™	
	45L	180L	Galaxy® S41i	Galaxy® 170	142L & 167L	150	240	IsoTemp™ 184	5.3A	8.5A
Orbi-Shaker CO <sub>2</sub> (14 x 12" platform)	*	●	●	●	●	●	●	●	●	●
Orbi-Shaker CO <sub>2</sub> XL (16 x 16.5" platform)	N/A	●	N/A	●	●	●	●	●	●	●
Orbi-Shaker CO <sub>2</sub> XL (18 x 18 platform)	N/A	N/A	N/A	N/A	●	N/A	●	●	N/A	●

\* Compatible 9.5 x 11.5" (Item: H1000-MR) available



Touch Screen, remote controller adjusts shaker settings from outside of the chamber and magnetically attaches to most incubators

### Technical Data

Speed Range:	30 to 300 rpm
Speed Increment:	1 rpm
Orbit:	19mm
Max. Capacity:	
BT4001	2 x 2L or 5 x 1L Flasks
BT4011	5 x 2L or 9 x 1L Flasks
Platform Dimensions:	
Included with BT4001:	13 x 12 in. / 33 x 30 cm
Included with BT4011:	16 x 16.5 in. / 40.5 x 42 cm
Ambient Operating Temp:	0° to 65°C
Weight:	BT4000: 25 lbs / 11.3 kg BT4010: 50lbs / 22.7 kg
Dimensions:	
BT4001 Shaker:	11.9 x 13.4 x 3.5 in. 30 x 34 x 9 cm
BT4011 Shaker:	17 x 18 x 5 in. 43 x 45.75 x 12.7 cm
Cord Length:	60.5 in. / 154 cm
Electrical:	115V Or 230V, 50-60Hz*

### Ordering Information

**BT4001\*** Orbi-Shaker CO<sub>2</sub>, Shaker with remote control, includes 13x12" non-slip platform, 115V

**BT4011\*** Orbi-Shaker CO<sub>2</sub> XL, Shaker with remote control, includes 16x16.5" non-slip platform, 115V

\*To order item in 230V, add (-E) to item number.

### Optional - Universal Platforms

BT3000-MR	MAGic Clamp universal platform for BT4001 (14x12")
BT4010-MR	MAGic Clamp universal platform for BT4011 (16x16.5")
H1010-MR	MAGic Clamp universal platform for BT4011 (18x18")

### Flask & Tube Rack Accessories for MAGic Clamp Platforms

H1000-MR-50	Flask Clamp, 50ml (BT4001: max. 30 / BT4011: max. 49*)
H1000-MR-125	Flask Clamp, 125ml (BT4001: max. 20 / BT4011: max. 36*)
H1000-MR-250	Flask Clamp, 250ml (BT4001: max. 14 / BT4011: max. 25*)
H1000-MR-500	Flask Clamp, 500ml (BT4001: max. 9 / BT4011: max. 16*)
H1000-MR-1000	Flask Clamp, 1000ml (BT4001: max. 5 / BT4011: max. 9*)
H1000-MR-2000	Flask Clamp, 2000ml (BT4001: max. 2 / BT4011: max. 5*)
H1000-MR-1550	Tube Rack, 12x50 & 21x15 ml tubes (BT4001: max.2 / BT4011: max. 4*)
H1000-MR-T15	Tube Rack, 32x15 tubes (BT4001: max. 3 / BT4011: max. 8*)
H1000-MR-T50	Tube Rack, 15x50 tubes (BT4001: max. 3 / BT4011: max. 8*)
H1000-MR-T600	Bottle Rack, 4x500/600ml conical bottles (BT4001: max. 2 / BT4011: max. 4*)

\*Maximum capacity listed for the BT4011 with the optional H1010-MR MAGic Clamp Platform.

**Benchmark**  
Scientific

PO Box 709 Edison, NJ 08818  
Phone: 908-769-5555 Fax: 732-313-7007  
Web: www.BenchmarkScientific.com  
Email: Info@BenchmarkScientific.com