TML Pam E-3001C

# TML

# PORTABLE DATA LOGGER





RESEARCH EQUIPMENT CO.,LTD.


# Field use, battery drive

This portable data logger consists of a control unit (TDS-150) and exclusive decade channel units (FSW-10) and measures strain gauges, strain-gauge-based transducers, DC voltages, thermocouples and Pt RTD. The decade channel unit (FSW-10) can be cascaded up to 5 units to total 50 channels. In addition, by using a switching box/TML-NET driving board (option), up to 100 channels can be extended. TDS-150 operates on not only AC mains but alkaline D-cells or battery and has data memory and sleep interval timer functions for long term automatic measurement. It is possible to store measurement data and setup condition on compact flash memory card. Interfaces are USB and RS-232C, and reading of various setting conditions and measurement data can be conducted from a PC.



#### **FEATURES**

- Connectable Five decade channel units (FSW-10) for 50 channels max.
- Possible long-term automatic measurement using sleep interval timer.
- Low power consumption
- Measurement of strain, DC voltage and temperature using thermocouples and Pt RTD.
- Large capacity data memory available.
- 1-gauge 4-wire method available.
- TEDS compatible
- Strain complete compensation method available
- Connectable network modules (Factory installed option)



expandable upto 50 channels


Channel unit FSW-10 (option)

TML-NET driving board (Factory-installed option) connectable for digital network measurement

Control unit TDS-150 with Battery unit

**RESEARCH EQUIPMENT CO., LTD.** 

### System block diagram



#### **INTERFACE**

#### USB port

Using the USB cable CR-6187 (option), control of TDS-150 from a computer and data read of online measurement are possible. The USB driver is contained in TML measurement software Visual LOG Light (option).

#### RS-232C port


By connecting the RS-232C cable CR-5360 (option), control of TDS-150 from a computer and data read of online measurement can be done. Also, connection with external devices using the external cable is possible.

- Monitoring on TML External Display EDU-11 The use of EDU-11 enables monitoring at a place away from TDS-150.
- Measurement with Remote Power Controller RPC-05A By setting up RPC-05A between TDS-150 and a computer or modems, power on/off, control for solar power charge, etc. in long-term measurement are possible.
- Printout of data


The measured data and stored data are printed on the external printer DPU-H245AS-A03A (option).

#### DATA MEMORY

The maximum 80,000 data can be recorded. The data memory is one area only and the data stored in the area in order of measurement. One data are composed of channel, measurement time, measured data and physical unit



## Pop-up operation guide



header, and time

Record of measured data in data memory, CF, and both

# Various applications

1-Gauge 4-Wire strain measurement method Patented






TDS-150

#### TML-NET for 2-wire digital network measurement

Strain gauge-based transducers : Load cells, Displacement transducers Civil engineering transducers, etc.





Compact design enabling to store in any storage box



#### Number of channels

	In conjunction with external switching box
	NB: Switching box/TML-NET driving board
	(Factory-installed option) is required.
50 channels	In conjunction with 5 units of FSW-10

#### Applicable sensors (Sensor mode setting)

		- 3/
	1-gauge 4-wire 120Ω method 240Ω	
	350Ω	
	3-wire quarter 120Ω	
Strain	bridge 240Ω	Bridge excitation voltage
Strain	350Ω	DC1V 48ms (50Hz)
	Half bridge 120~1000Ω	
	Full bridge 120~1000Ω	
	Full bridge con- 350Ω stant current	
	Full bridge 0-2V 120~1000Ω	Bridge excitation voltage DC2V 24ms (50Hz)
Thermo- couple	Thermocouple T Thermocouple K Thermocouple J Thermocouple B Thermocouple S Thermocouple R Thermocouple E Thermocouple N	Linearization: Digital operation
DC voltage	Voltage V 1/1 ±300mV Voltage V 1/100 ±30V	Input impedance V 1/1 more than 500MΩ V 1/100 more than 1MΩ
Pt RTD	Pt RTD 3-wire	Linearization: Digital operation
TML-NET	Operating NSW series [Option]	Data reading from Network sensors

#### Measuring Range

Item	Range	Measuring range	Initial memory	Sampling speed
Strain	x1 x10	±30000 x10 <sup>-6</sup> strain ±300000 x10 <sup>-6</sup> strain	±160000 x10 <sup>-6</sup> strain	
	x1 x10	V 1/1 ± 30.000mV ±300.000mV	V 1/1 ±160.000mV	80ms
DC voltage	x1 ± 3.0000 V x1 ± 3.0000 V x10 ±30.0000 V		V 1/100 ± 16.0000V	(50Hz area) 67ms (60Hz area)
Thermo- couple	_	T: - 250 ~ + 400°C K: - 210 ~ +1370°C J: - 200 ~ +1200°C B: +200 ~ +1760°C S: - 10 ~ +1760°C R: - 10 ~ +1760°C E: - 210 ~ +1000°C N: - 200 ~ +1300°C	_	
Pt RTD	—	- 200 ~ +850°C	—	

Note : Measuring range in Full bridge 0-2V mode for TML LVDT is ±15000 x10<sup>-6</sup> strain (x1) and 150000 x10<sup>-6</sup> strain (x10).

#### Measuring accuracy

Sensor mode	Range	Resolution	Accuracy (23°C±5°C)	Tempera- ture effect (%rdg/°C)	Aging effect (%rdg/year)
Strain	×1	1x10 <sup>-6</sup>	±(0.08%rdg+1digit)	±0.002	±0.02
	×10	10x10 <sup>-6</sup>	±(0.08%rdg+1digit)	±0.002	±0.02
DC voltage	×1	0.001mV	$\pm$ (0.08%rdg+3digit)	±0.0024	±0.02
V1/1	×10	0.010mV	$\pm$ (0.08%rdg+3digit)	±0.0024	±0.02
DC voltage	×1	0.0001V	±(0.08%rdg+2digit)	±0.002	±0.02
V 1/100	×10	0.0010V	±(0.08%rdg+2digit)	±0.002	±0.02
Pt RTD Pt100 3W	_	0.1°C	±(0.08%rdg+3°C)	±0.0020	±0.05

Range : in auto-ranging

#### Leadwire resistance correction

Comet B (3-wire guarter bridge)	Gauge resistance	Leadwire resistance correction range
(	120Ω	Less than 100Ω
	240Ω	Less than 200Ω
	350Ω	Less than 300Ω

#### Thermocouple temperature measurement

		Thermo- Measuring range Resolution Accuracy ±(%rdg+°C) (23°C±5°C)				
(00)						
(°C)	(°C)	External RJC	Internal RJC			
250 ~ - 200	0.1	0.38 + 0.6	0.38 + 3.9			
200 ~ - 100	0.1	0.15 + 0.2	0.15 + 1.4			
100 ~ + 400	0.1	0.10 + 0.2	0.10 + 0.8			
210 ~ - 160	0.1	0.19 + 0.3	0.19 + 1.6			
160~ 0	0.1	0.12 + 0.2	0.12 + 1.0			
0~+ 960	0.1	0.08 + 0.1	0.08 + 0.5			
960 ~ +1370	0.1	0.10 + 0.9	0.10 + 1.4			
200 ~ - 160	0.1	0.16 + 0.2	0.16 + 1.2			
160~ 0	0.1	0.12 + 0.1	0.12 + 0.8			
0~+ 700	0.1	0.08 + 0.1	0.08 + 0.5			
700 ~ +1200	0.1	0.08 + 0.6	0.08 + 0.9			
200 ~ + 280	0.5~0.4	0.04 + 4.0	0.04 + 4.0			
280 ~ + 800	0.3~0.1	0.04 + 1.2	0.04 + 1.2			
800 ~ +1760	0.1	0.05 + 0.4	0.05 + 0.4			
10 ~ + 200	0.1	0.09 + 0.6	0.09 + 1.2			
200 ~ +1760	0.1	0.07 + 0.4	0.07 + 0.7			
10 ~ + 150	0.1	0.09 + 0.7	0.09 + 1.2			
150 ~ +1760	0.1	0.07 + 0.4	0.07 + 0.7			
210 ~ + 550	0.1	0.17 + 0.2	0.17 + 1.4			
550 ~ +1000	0.1	0.09 + 0.4	0.09 + 0.8			
200 ~ 0	0.1	0.18 + 0.4	0.18 + 1.6			
0 ~ +1090	0.1	0.08 + 0.2	0.08 + 0.6			
090 ~ +1300	0.1	0.08 + 0.9	0.08 + 1.2			
	$\begin{array}{c} 200 & - & - & 100\\ 100 & - & + & 400\\ 210 & - & - & 160\\ 160 & & & 0\\ 00 & + & 960\\ 960 & - & +1370\\ 200 & - & - & 160\\ 160 & & & 0\\ 00 & + & 700\\ 700 & - & +1200\\ 200 & - & + & 280\\ 280 & - & + & 800\\ 800 & - & + & 1760\\ 10 & - & + & 250\\ 150 & - & + & 1760\\ 150 & - & + & 1760\\ 200 & - & + & 1760\\ 200 & - & + & 1760\\ 200 & - & + & 1760\\ 200 & - & + & 1760\\ 200 & - & 0\\ 00 & - & + & 1090\\ 090 & - & + & 1300\\ \end{array}$	$\begin{array}{cccccccccccccccccccccccccccccccccccc$	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$			


The accuracy of thermocouples is not included. Thermocouple B does not use RJC. RJC: Reference junction compensation

	Display unit	LCD with backlight	
Display	Resolution	255x160 dot	
,	Contents	Measuring data, Setting list, Y-T monitor	
	Setting	Year, Month, Day, Hour, Min. and Sec.	
Clock	Accuracy	$\pm 1 \text{ sec./day}$ (23°C $\pm 5$ °C)	
	USB/RS-232C, LAN (Option)		
Interface	Function	Control from PC and Data transfer	
Measurement	INITIAL, DIRE	CT & MEASURE for each channel	
mode	(DIRECT only	for temperature)	
<u>.</u>	Scanning	Automatically from First to Last channel	
Channel		(Jump available)	
switching	Monitor	Repetition of monitor channel	
		Time-independent graphic monitor	
Measurement		h, Interval timer, Monitor comparator	
start		and LAN (Option)	
	Capable of set	ting for each channel	
	Coefficient	±(0.0001 to 99999)	
Program	Unit	40 kinds such as με, mV, °C, kN and mm	
	Decimal point	Any 0 ~ 6 decimal places	
	Initial value	Writing for every channel	
	Sesor mode	Setting for every sensor	
	Coefficient	1.0000	
SIMPLE	Unit	As per sensor mode	
measure	Decimal point	As per sensor mode	
Self-diagnosis	Insulation resistance, Dispersion, Sensitivity, Thermocouple wire burnout, Bridge output and coefficient setting		
TEDS	Standard	IEEE1451.4 Class 2	
TEDS	Function	Readout of TEDS sensor parameter	
	Function	Automatic start according to the set time interval and time	
	Interval	Hour, min. and sec. up to 99h 59m 59s for	
		each step	
	No. of starts	Programmable 99 times at max. or infinite per step	
Interval timer	No. of steps	Programmable 10 steps at max.	
	Real time start	• ·	
	GOTO step	Looping previous step	
	Sleep ON/OFF	Switches on 5 sec. before measurement start and turns off automatically after measurement finish	
	Function	Automatic measurement based on a change	
Monitor com- parator		amount set by monitor channel (1point)	
paratur	Comparative	Amount settable every step (±999999 at max.)	

Monitor com-	Comparative method	Available either amount of change or absolute		
parator	Cycles of start	Max. 99 times/step or infinite		
	Cycles of step	Max. 10 steps programmable		
	GOTO step	Programmable loop to previous step		
	GOTO interval	Move to step 1 of interval		
	Function	Storing and reading of measurement data		
Data memory	Contents	Measure mode, channel number, measure- ment data, time data and data number		
Data memory	Capacity	Maximum 80000 data or 16,000 scans per 10 channels		
	Storage period			
Memory card	Standard	Compact Flash™ card		
wennory card	Capacity	32MB ~ 2GB (FAT 16)		
Auto-power OFF	Automatically turns off when neither receiving any key opera- tion nor interface commands for any set time. Switchable On/ Off.			
Operational time in con- tinuous use	Full bridge 120	alkaline battery Ω about 40 hours at 23°C±5°C terval about 8 months for 10 channels scanning, Sleep ON at 23°C±5°C		

Operational environ- ment	-10 ~ +50°C <85%RH without condensation				
Storing temperature	–20 ~	+60°C			
Power requirement	LR20 Alkaline cell 4 pieces Exclusive AC adaptor (CR-1861) External battery 9 ~ 18Vdc				
Dimensions	TDS-150 Control unit including battery unit 280(W) x 60(H) x 162(D) mm FSW-10 Unit channel (Option) 280(W) x 60(H) x 100(D) mm excluging projecting parts				
Weight	TDS-150 Control unit : 1.0 kg Battery unit : 0.6 kgs (No battery installed) FSW-10 Unit channel (Option) : 1.5 kgs.				
Standard accessory		LR20 Alkaline cell Philips driver Operation manual Carrying belt	4 pieces 1 piece 1 copy 1 piece		

#### **Outer View and Dimensional Diagram**



#### Channel Unit FSW-10

Combination with the exclusive switching box makes maximum 50 channels automatic and interval measurement possible.



#### **Remote Power Controller RPC-05A**

In combination with RPC-05A and an external battery, long-term measurement with TDS-150 using sleeping function becomes possible.




#### External Display Unit EDU-11

The monitor value of TDS-150 can be displayed at a remote place. Features high visibility with high-brightneess LED.

Data cable CR-3830 BNC output cable CR-31 belonging to EDU-11





#### External Printer DPU-H245AS-A03A

The measurement data of TDS-150 is printed out...



Printer cable CR-5370 optional Dsub9P-10P(mini) thru 0.5m Exclusive cable

RS-232C cable CR-5360 Dsub9P-9P Cross Exclusive cable for connection with personal computer

USB cable CR-6187 Mini B-A with ferrite core 1.5m Exclusive cable for connection with personal computer

AC adaptor CR-1861 Compact Flash<sup>™</sup> card Capacity : 32MB~2GB



#### **TEDS compatible sensor**

To use TEDS functioin of the TDS-150, TEDS compatible sensor is required to recognize its own parameters such as measuring capacity, rated output, etc. registered in the built-in IC chip.



TEDS compatible load cell TCLZ with the built-in IC chip



Approval Certificate **ISO9001** Design and manufacture of strain gauges, strain measuring equipment and transducers



• Tokyo Sokki Kenkyujo Co., Ltd. www.tml.ip/e

8-2, Minami-Ohi 6-Chome, Shinagawa-Ku, TOKYO 140-8560, JAPAN TEL: TOKYO 03-3763-5611 FAX: TOKYO 03-3763-5713 *e* -mail address:**sales@tml.jp** 

Specifications subject to change without prior notice

RESEARCH EQUIPMENT CO.,LTD.

201312WEB