DENSO

NEW BHT-15C



BHT-1500 series specification

| | | | Batch Model | Bluetooth® Model | | |
|---------------------------------------|----------------------------|------------------------|--|---------------------------------------|--|--|
| Models | | | BHT-1505B | BHT-1505BB | | |
| OS | | | BHT-OS | | | |
| CPU | | | 32bit RISC microprocessor | | | |
| Memory | Flash Memory | | 32MB (Approx. 17 MB for user area)*1 | | | |
| Display | The Number of Dots*2 | | 2.0 inch QVGA (240 x 320dots) | | | |
| | Display device | | Liquid crystal dot matrix display (color) | | | |
| | Backlight | | White LED | | | |
| Scanner | Mode | | Advanced Scan Plus (CCD) | | | |
| | Decode | Barcode | EAN-13/8 (JAN-13/8), UPC-A/E, UPC/EAN (Add-on embedded), Interleaved 2 of 5 (TF), Standard 2 of 5 (STF), CODABAR (NW-7), CODE39, CODE93, CODE128, GS1-128 (EAN-128), GS1 Databar (RSS) | | | |
| | Minimum resolution | | 0.125 mm | | | |
| | Reading reference position | | 110 mm | | | |
| | Scan Confirmation | | LED in three colors: Blue/red/green, Buzzer, Vibration | | | |
| Key input section | The Number of keys | | 21keys (including power key) + Cross-hair cursor key + a trigger key | | | |
| Communication | Optical I/F | Communication mode | Infrared ray (IrDA Ver.1.2 [Low Power] physical signaling layer-compliant) | | | |
| | | Transmission speed | ~115.2kbps, 460.8kbps | | | |
| | | Communication distance | Approx. 0.15 m MAX. | | | |
| | Bluetooth® | | _ | Bluetooth®2.1 + EDR (SPP/HID/DUN/GAP) | | |
| Card slot | | | microSDHC/microSD card (~32GB)×1 | | | |
| Power | Main battery | | Alkaline AAA battery × 3 or AAA eneloop® battery × 3 | | | |
| | Operating time*3 | Alkaline battery | 85 hours*4 | | | |
| | | eneloop® | 70 hours*4 | | | |
| Additional functionality | | | Clock, Buzzar, Vibelation, Battery and voltage indicators | | | |
| Environmental performance | Operating temperature | | -5 to 50°C*5*6 | | | |
| | Security level | | IP54 | | | |
| | Drop resistance*7 | | Dropped from 2.0 m/1.2 m above concrete floor, on all 6 faces, 10 times each (total 60 times) | | | |
| Mass (including AAA eneloop® battery) | | | Approx. 128 g | | | |
| , , | | , | The liquid panel is made with high-precision technology. | | | |
| | | | | | | |

understand that there is 0.01% chance of the display being scrambled and turned off. *3 Operating times shown are reference values at room temperature and may vary n working conditions. '4 In the case of once reading per 5 seconds. Backlight level is 1. '5 Operation temperature of eneloop®. '6 Zero to 40°C when batteries tharged. '7 Result obtained in a test under regular temperature is shown and not meant as a guarantee.

Option (sold separetely)

- Holder, which performs data communication with BHT communication unit and the up-level device
- CU-AU1-15 (USB communications + recharging)
- CU-AR1-15 (RS232C communications + recharging)
- CU-AL1-15 (Ethernet communications + recharging)

| Additional functionality | | | CU-AR1-15 | CU-AL1-15 | CU-AU1-15 |
|--------------------------|----------------------|--------------------|--------------------|----------------------|-----------------------------------|
| Communication | Between BHT and host | Communication mode | RS-232C | Ethernet(100BASE-TX) | USB2.1 Full speed mode-compatible |
| Charging | Charging time | | Approx. 5 hours | | |
| Size (mm) | | | 110(D)×95(W)×98(H) | | |
| Working voltage | | | | AC adapter | Supplied from USB port/AC adapter |

^{*} The AC adapter is sold separately

Communication cable

- CBBHT-US2000/C15-4A
- * BHT-1500 can be recharged by connecting it to a USB charger or other power adapter, or a PC USB port. When recharging the BHT-1500, use a device that satisfies the following output and USB

- charging specifications: DC5±0.25V (power voltage); 1.0 A or higher (power current) USB charging specifications: Battery Charging Specification, Rev 1.2

Recharger

• CH-A4-15 (4 serial battery rechargers)


Soft case and others

- SCBHT-900/1500 (soft case)
- WHBHT-1500 (waist case) NSBHT-1300 (neck strap)

Components

- Guidelines for operation Instruction manual Ψ
- Hand strap
- * Batteries and eneloop® are not supplied with this product

 \bullet Before using this product, please read its User's Manual thoroughly for correct use.



Software (sold separately)

Development tools

• BHT-BASIC4.0 Creator

| Deelere | BHT-BASIC4.0 Creator |
|----------|-------------------------------|
| contents | BHT-BASIC4.0 transfer utility |
| Contents | BHT-BASIC4.0 simulator |

BHT Advanced Pack II

☐ • BHT Advanced Pack II Package

Application production tool/communication tool BHT-BASIC4.0 simulator

Assist Pack Pro (produced by Computer Assist Co., Ltd.)

Preinstalled software

• Easy Pack Ad for BHT-1500

Software for setting

• BHT Setting 🖳

Items with this mark are available from the company's homepage (QBdirect) free of charge.

For more information, please visit our website http://www.denso-wave.com/en/adcd/

Featuring the function of "lightness"



[Full size] * Conceptual image



244 Soi Pattanakarn 53, Pattanakarn, Suanluang, Bangkok 10250 Thailand

Tel: (66) 0-2322-9535, 0-2722-4040 Fax: (66) 0-2322-7990

www.cps.co.th • www.facebook.com/cps.co.th







Basic functions packed into the compact body

Light, eye-friendly and contoured



■ BHT-1500 series can be used in a wide variety of situations.



Lightest-in-class compact body

BHT-1500 series has a light, compact and highly portable body weighing just 128 grams, the lightest in the industry among handheld terminals in the same class. This helps maximize productivity as the operators can use the device for lengthy periods with no physical strain on themselves.



Largest-in-class 2.0-inch color liquid crystal screen

BHT-1500's compact body is equipped with a 2.0-inch QVGQ colour liquid crystal screen, the largest among handheld terminals in its class. The ensures that application screens and product images are displayed very clearly helping reduce operator errors.



Quick scanning performance

With its unique scanning angle and high performance barcode reader the BHT-1500 series users can scan barcodes while viewing the screen, enabling efficient work in the field.



Excellent operability. Contoured body with well laid out keys

The ergonomically designed BHT-1500 sits comfortably in your hand and well positioned keys enable single handed use.



Excellent durability

Since BHT-1500 series is resistant to drops from a height of 2.0 meters, you can use it for daily operation with peace of mind.

Reliable even when accidents happen

Should the battery be disconnected, the transaction function automatically restores the device to the previous status in the application. the flash file system will retain inputted data without the need for batteries, ensuring relable device performance and confidence your data will not be lost.



A microSDHC card can be used as an external memory

When you need to store large files or increased data a microSDHC card can be used providing

Many convenient functions, enabling easy adoption

Excellent application compatibility with existing models

BHT-1500 series has excellent compatibility with applications developed for existing models with BHT-BASIC. With the display compatibility mode, applications developed for BHT-900 can be used without changing the display layout settings.



Files can be easily transferred by connecting the device via USB to your PC

Data can easily be transferred by simply dragging and dropping. So you can be operational with minimal effort.



eneloop® can be used. Recharging time is reduced by half compared to existing models*1

In addition to convenient dry-cell batteries, BHT-1500 can use eneloop rechargeable batteries. The device can be fully recharged in 5 hours - about half time of previous models.





Can be connected to a tablet or smartphone via Bluetooth®

* BHT-1500BB model on

BHT-1500BB model is Bluetooth HID-enabled, enabling easy data transfer to tablets and smartphones.



3-year warranty provides peace of mind

DENSO WAVE provides a three-year warranty to customers who have registered on its website, giving peace of mind. Our customer service personnel and sales representatives quickly respond to any issue our customers may experience including device failures and make every effort to ensure that customers can use DENSO WAVE's handheld terminals with confidence.



Can be used immediately. The basic operation application "Easy Pack Ad" is preinstalled

"Easy Pack Ad" is a preinstalled application that can be used for collection of data verification and other basic operations. You can start operations immediately without developing any additional applications.

