



บรรจุถุงละ 25 กิโลกรัม

Active clear glass

- ▶ ประสิทธิภาพในการกรองมากกว่า เป็นมิตรกับสิ่งแวดล้อม
- ▶ มีพื้นที่การกรองมากขึ้น
- ▶ ประหยัดน้ำและพลังงาน
- ▶ ทำความสะอาด กรองเชื้อแบคทีเรีย ไรต์ที่ไม่ได้อยู่ติดกับดักและผลิตภัณฑ์เคมี ที่มีขนาดเล็ก
- ▶ Active Clear Glass complies with standard UNE EN 12902:2066.



Code:57011

ความละเอียด 0.5- 1.0 mm



57012

1.0- 3.0 mm



57013


3.0- 7.0 mm



	Code	Range	%VOLUME OF THE FILTER BED	
			Filter D<900 mm	Filter D>900 mm
Range1	57011	0,50 - 1,00 mm	80%	60%
Range2	57012	1,00 - 3,00 mm	0%	20%
Range3	57013	3,00 - 7,00 mm	20%	20%

QUALITY of filtration

คุณภาพการกรอง



The results obtained show that the final quality of the Active Clear Glass filter is better than a sand filter. In the activated glass filter, the final quality of filtration reached 1.5 NTU after one hour in operation under test conditions. After working for one hour, the cloudiness of the water filtered through the Active Clear Glass system fell by over 90%.

Comparative table of current filter media

MATERIAL	FLUSHING	QUALITY OF FILTRATION	RECYCLING
Sand	●	●	●
Standard glass	●	●	●
Active Clear Glass	●	●	●

FLUSHING: Water flow required for backwashing filters.
QUALITY: Final level of cloudiness reached using an equivalent sample.
RECYCLING: Number of times water has to be renewed.